

Lamp replacement guide for Motic microscopes

09-Dec-13

Model	Rating	Product code	Alternatives
TT-52L	Tungsten 240V/15W	240V15WSCB-FLUSH	N/A
TT-52LED-MV/ BA50/ BA80 series	LED 20mA, 3.5V, 70mQ	MA-11.010.026.0016.1	N/A
AIS-260 series/ B1 series	Halogen 12V/20W	12V20WHAL	Yes
AIS-M2L/ AIS-M100FL	Tungsten bulb 240V/20W	MA-11.010.024.0052.3	N/A
S-20-LO	Tungsten 12V/10W	12V10W FESTON	N/A
ST-36C-2LGO (incident)	Halogen 12V/20W	12V20WHAL	Yes
ST-36C-2LGO (transmitted)	Tungsten 12V/10W	12V10W FESTON	N/A
BA210/ BA310/ BA310POL /BA410/ AE2000/ AE30 (Halogen)	Halogen 6V/30W	6V30WHAL	Yes
BA210E/BA310E (LED)	3W LED	MA-11.010.024.0002.2	N/A
BA310MET/ BA310MET-H/ AE2000MET (Epi Illuminator)	Halogen 12V/50W	MA-11.010.024.0243.1	N/A
BA310MET-T (Transmitted)/	Halogen 6V/30W	6V30WHAL	Yes



SMZ-140-N2GG (Incident)

Halogen 12V/15W

12V15WHAL

Yes



SMZ-140-N2GG (Transmitted)

Halogen 12V/10W

12V10WHAL

Yes



SMZ-140-FBGG (Incident)/ SMZ-168 (Incident)

Halogen 12V/10W with reflectiv MA-11.010.024.0037.2

N/A



SMZ-140-FBGG (Transmitted)/ SMZ-168 (Transmitted)

Halogen 12V/10W

12V10WHAL

N/A



SMZ-161-TL (Incident)

Halogen 12V/10W with reflectiv MA-11.010.024.0037.2

N/A

SMZ-161-TL (Transmitted)

Halogen 12V/20W

MA-11.010.024.0352.1

N/A

SMZ-171-TLED (Incident)

SMZ-171-TLED (Transmitted)

